

Standards Reference Guide



Anixter: The Cabling System Experts

Anixter is the world's leading supplier of communication products used to connect voice, video, data and security systems. Anixter is also the leading provider of electrical and electronic wire and cable, fasteners, and other small components to build, repair, and maintain a variety of systems and equipment. We bundle our products with our innovative Supply Chain Services to cut costs out of our customers' business processes, and ensure they get the right product, the first time.

You can look to Anixter when you need any type of communication infrastructure. Whether you're looking for data, voice or video networks, wired or wireless, in an office, campus or factory, Anixter is the company to turn to. We are the one distributor with both the technical savvy to help you determine the right products for your application and the unparalleled global distribution capabilities to get you that product, when and where you need it. In an effort to continually support you, we have pulled together some valuable information from ANSI/TIA/EIA, ISO and IEEE.

The information contained within this reference guide covers the key aspects of the ANSI/TIA/EIA-568-B, 568-B.2-1, 568-B.2-ad10, 569-B, 606-A, J-STD-607-A, 942, IEEE 802.3af, IEEE 802.3an, IEEE 802.11 and ISO 11801 standards. We hope you find its contents informative and useful.

Scope of this Handbook

This document is meant as a reference that highlights the key points of the ANSI/TIA/EIA-568-B, 569-B, 606-A, J-STD-607-A, 942 and IEEE 802.3af, IEEE 802.3an, IEEE 802.11 and ISO 11801 standards. It is not intended as a substitute for the original documents. For further information on any topic in the guide, refer to the actual standard. See the section called "Reference Documents" for instructions on how to order a copy of the standard itself.

Abbreviation References:

ANSI American National Standards Institute
ASTM American Society for Testing and Materials

CSA Canadian Standards Association
FIA Flectronic Industries Alliance

IEC International Electrotechnical Commission

IEEE Institute of Electrical & Electronic Engineers

ISO International Organization for Standardization

NEC National Electric Code

NEMA National Electrical Manufacturers Association

NFPA National Fire Protection Association

TIA Telecommunications Industry Association



Standards Reference Guide

4

Table of Contents

ANSI/TIA/EIA-568-B, Commercial Building	
Telecommunications Cabling Standard	5
568-B.1, General Requirements	
568-B.2, Balanced Twisted Pair Cabling Components	
568-B.2-1, Category 6 Transmission Performance	
TIA/EIA-568-B.2- Addendum 10, Augmented Cat 6	
Transmission Performance	32
TIA/EIA-568-B.3, Optical Fiber Cabling Components	34
ANSI/TIA/EIA-569-B, Pathways and Spaces	36
ANSI/TIA/EIA-606-A, Administration	
J-STD-607-A, Grounding and Bonding	60
ANSI/TIA/EIA-942	
Purpose of the ISO 11801:2002 Standard	73
ISO 11801, Class E _A	74
IEEE 802.3af Power over Ethernet	
IEEE 802.11 Wireless	76
IEEE 802.3an	78
Anixter Enterprise Cabling and Security Labs	80
Reference Documents	

Purpose of the ANSI/TIA/EIA-568-B Standard

The Purpose:

- Establish a generic telecommunications cabling standar that will support a multivendor environment
- Enable the planning and installation of a structured cabling system for commercial buildings
- Establish performance and technical criteria for various cabling system configurations

The Standard Specifies:

- Minimum requirements for telecommunications cabling within an office environment
- Recommended topology and distances
- Media parameters which determine performance
- · Connector and pin assignments to ensure interconnectability
- The useful life of telecommunications cabling systems as being in excess of 10 years

Building telecommunications cabling specified by this standard is intended to support a wide range of different commercial building sites and applications (e.g., voice, data, text, video and image). Typically, this range includes sites with a geographical extent from 10,000 to 10,000,000 sq ft (3,000-1,000,000 m²) of office space, and with a population of up to 50,000 individual users.

This standard replaces ANSI/TIA/EIA-568-A dated October 6, 1995.

This standard also incorporates and refines the technical content of TSB67, TSB75, TSB95 and TIA/EIA-568-A-1, A-2, A-3, A-4 and A-5.

Standards Reference Guide

more information, visit www.anixter.com or call 1.800.Anixter.

Section Contents


ANSI/TIA/EIA-568-B

Commercial Building Telecommunications Cabling Standard TIA/EIA-568-B.1 General Requirements

The Six Subsystems of a Structured Cabling System	
Entrance Facilities	
Equipment Room	
Backbone Cabling9	
Design Requirements)
Telecommunications Room	
Horizontal Cabling	
Specified Topology	
Maximum Distances	
MUTOA	
Consolidation Point	
Centralized Optical Fiber	
Work Area	
Work Area Components	
Telecommunications Outlet	
8-Position Modular Jack Pair Assignments	
Channel and Permanent Link	
Definitions of Electrical Parameters	
TIA/EIA-568-B.2 Balanced Twisted Pair Cabling Components	
100 Ohm Unshielded Twisted Pair Cabling Systems	1
Horizontal and Backbone Cable	
Bundled and Hybrid Cable	
LITP Connecting Hardware 21	

26
27
.28
29
.30
.30
31
32
33
34
34
35
35
35
35
35

TIA/EIA-568-B.1 General Requirements



The Six Subsystems of a Structured Cabling System

1. Entrance Facilities (EF)

Building entrance facilities (EF) provide the point at which outdoor cabling interfaces with the intrabuilding backbone cabling. The physical requirements of the network interface are defined in the TIA/FIA-569-B standard.

2. Equipment Room (ER)

The design aspects of the equipment room are specified in the TIA/EIA-569-B standard. Equipment rooms usually house equipment of higher complexity than telecommunication rooms. Any or all of the functions of a telecommunications room may be provided by an equipment room.

3. Backbone Cabling


The backbone cabling provides interconnection between telecommunication rooms, equipment rooms and entrance facilities. It consists of the backbone cables, intermediate and main cross-connects, mechanical terminations and patch cords or jumpers used for backbone-to-backbone cross-connection. This includes:

Technol ogy.

Servi ces.

Delivered Globally

- Vertical connection between floors (risers)
- Cables between an equipment room and building cable entrance facilities
- Cables between buildings (inter-building)



Specified Backbone Cabling Topology: Star

Other Design Requirements

- Star topology
- No more than two hierarchical levels of backbone cross-connects
- · Bridge taps are not allowed
- Main and intermediate cross-connect jumper or patch cord lengths should not exceed 20 m (66 ft)
- Avoid installing in areas where sources of high levels of EMI/RFI may exist
- Grounding should meet the requirements as defined in J-STD-607-A

Note: It is recommended that the user consult with equipment manufacturers, application standards and system providers for additional information when planning shared-sheath applications on UTP backbone cables.

Maximum Backbone Distances						
Media Type Copper (Voice*)	Main to Horizontal Cross-Connect 800 m (2,624 ft)	Main to Intermediate Cross-Connect 500 m (1,640 ft)	Intermediate to Horizontal Cross-Connect 300 m (984 ft)			
Multimode	2,000 m (6,560 ft)	1,700 m (5,575 ft)	300 m (984 ft)			
Single-mode	3,000 m (9,840 ft)	2,700 m (8,855 ft)	300 m (984 ft)			

*Note: Backbone distances are application-dependent. The maximum distances specified above are based on voice transmission for UTP and data transmission over fiber. A 90 m distance applies to UTP at spectral bandwidths of 5-16 MHz for Cat 3 and 20-100 MHz for Cat 5e. Current state-of-the-art distribution facilities usually include a combination of both copper and fiber optic cables in the backbone.

4. Telecommunications Room (TR)

A telecommunications room is the area within a building that houses the telecommunications cabling system equipment. This includes the mechanical terminations and/or cross-connects for the horizontal and backbone cabling system. Please refer to TIA/EIA-569-B for the design specifications of the telecommunications room.

Technol ogy.

Services. Delivered Globally

5. Horizontal Cabling

Specified Horizontal Cabling Topology: Star


The horizontal cabling system extends from the work area telecommunications information outlet to the telecommunications room and consists of the following:

- Horizontal cabling
- Telecommunications outlet
- Cable terminations
- Cross-connections
- Patch cords

Four media types are recognized as options for horizontal cabling, each extending a maximum distance of 90 m:


- 4-pair, 100 ohm UTP/ScTP cable (24 AWG solid conductors)
- 2-fiber, 62.5/125 µm or 50/125 µm optical cable

Maximum Distances for Horizontal Cabling



In addition to the 90 m of horizontal cable, a total of 10 m is allowed for work area and telecommunications room patch and jumper cables.

Multi-user Telecommunications Outlet Assembly (MUTOA) Optional practices for open office environments are specified for any horizontal telecommunications cabling recognized in TIA/EIA 568-B.



A multi-user telecommunications outlet assembly (MUTOA) facilitates the termination of multiple horizontal cables in a common location within a column, wall or permanently secured furniture cluster. Work area cables may then be routed through furniture pathways and directly connected to work area equipment. Each furniture cluster should have one MUTOA which serves a maximum of 12 work areas. Ceiling and access floor mounting is not allowed by TIA/EIA-569-B.

Maximum work area cable length is determined by the following table:						
Length of	Maximum	Maximum combined length				
horizontal	length of work	of work area cables, patch				
cable m (ft)	area cable (24AWG) m (ft)	cords and equipment cable m (ft)				
90 (295)	5 (16)	10 (33)				
85 (279)	9 (30)	14 (46)				
80 (262)	13 (44)	18 (59)				
75 (246)	17 (57)	22 (72)				
70 (230)	22 (72)	27 (89)				

Servi ces.

Delivered Globally

Note: No work area cable length may exceed 22 m (72 ft).

For optical fiber, any combination of horizontal, work area cables, patch cords and equipment cords may not exceed 100 m (328 ft).

Consolidation Point




A consolidation point differs from a MUTOA in that it requires an additional connection for each horizontal cable run. Only one consolidation point (an interconnection point in the horizontal cabling) is allowed at a distance of at least 15 m (49 ft) from the telecommunications room. A transition point (transition from round to flat under carpet cable) is not allowed. A consolidation point is installed in unobstructed building columns, permanent walls, ceilings or access floors (if accessible).

The multi-user telecommunications outlet and consolidation point methods are intended to be mutually exclusive. Labeling and allowance for spares is required. Moves, adds and changes should be administered in the telecommunications room.

Centralized Optical Fiber Cabling

The ANSI/TIA/EIA-568-B.1 standard offers maximum flexibility for distributed electronics for multi-tenant buildings by providing for single-tenant users who prefer centralized electronics (i.e., server farms) connected by a fiber horizontal and fiber backbone.



Centralized Cabling Scheme

To connect fiber from the work area to the equipment room within a single building, the user may use a splice or interconnect in the telecommunications room. The combined distance limitation is 300 m (984 ft) for horizontal, intrabuilding backbone and patch cords. Alternatively, the user may simply pull cables through the closet. In this last case, the fiber horizontal and backbone consist of one continuous fiber pair, and the pull-through distance limitation is 90 m (295 ft). Cabling is 62.5/125 μm multimode or 50/125 μm multimode. Sufficient space should be allowed for slack, addition and removal of cables, spares and conversion to a full cross-connect system. Labeling should be in accordance with TIA/EIA-606-A with additional labeling to identify A-B pairs with specific work areas.

6. Work Area (WA)

The work area components extend from the telecommunications (information) outlet to the station equipment. Work area wiring is designed to be relatively simple to interconnect so that moves, adds and changes are easily managed.

Work Area Components

- Station equipment computers, data terminals, telephones, etc.
- Patch cables modular cords, PC adapter cables, fiber jumpers, etc.
- Adapters baluns, etc. (must be external to telecommunications outlet)


Technol ogy.

Servi ces.

Delivered Globally


Telecommunications Outlet

Each work area should have a minimum of two information outlet ports, one for voice and one for data.




Telecommunications Outlet

8-Position Modular Jack Pair Assignments for UTP



Channel and Permanent Link

For the purpose of testing UTP cabling systems, the horizontal channel is assumed to contain a telecommunications outlet/connector, a transition point, 90 m of UTP cable, a cross-connect consisting of two blocks or panels and a total of 10 m of patch cords. The figure below shows the relationship of these components.



Two link configurations are defined for testing purposes. The permanent link includes the horizontal distribution cable, telecommunications outlet/connector or transition point and one horizontal cross-connect component including the mated connections. This is assumed to be the permanent part of a link. The channel is comprised of the permanent link plus cross-connect equipment, user equipment cord and cross-connect patch cable.

Technol ogy.

Delivered Globally

Minimum Bend Radius	
Horizontal UTP (4-pair)	4 x diameter
Horizontal ScTP	8 x diameter
Backbone Cable	10 x diameter
Patch Cord	Not determined

Physical requirements of 4-pair UTP:

Maximum diameter: 1/4 inch Breaking strength: 90 lbs.

Maximum pulling tension: 25 lbs.

Definitions of Electrical Parameters

Insertion Loss: This term has replaced the term "attenuation" (ATTN). It is a measure of the decrease of signal strength as it travels down the media.

NEXT (near-end crosstalk): A measure of the unwanted signal coupling from a transmitter at the near-end into a neighboring (non-energized) pair measured at the near-end.

PSNEXT (powersum near-end crosstalk): A computation of the unwanted signal coupling from multiple transmitters at the near-end into a neighboring (non-energized) pair measured at the near-end.

FEXT (far-end crosstalk): A measure of the unwanted signal coupling from a transmitter at the near-end into a neighboring pair measured at the far-end.

ELFEXT (equal-level far-end crosstalk): A measure of the unwanted signal coupling from a transmitter at the near-end into a neighboring pair measured at the far-end, relative to the received signal level measured on that same pair. Referred to as ACR-F (insertion loss to crosstalk ratio far-end) in the TIA/EIA-568-B.2-Addendum 10 draft. (ELFEXT is FEXT adjusted to discount insertion loss.)

PSAACRF (powersum insertion loss to alien crosstalk ratio far-end):

A computation of signal coupling from multiple pairs of disturbing channels, to a disturbed pair in another channel measured at the far-end and relative to the received signal level in the disturbed pair at the far-end. Also referred to as powersum alien equal-level far-end crosstalk (PSAELFEXT).

PSANEXT (powersum alien near-end crosstalk): A computation of signal coupling from multiple near-end disturbing channel pairs into a disturbed pair of a neighboring channel or part thereof, measured at the near-end.

PSAFEXT (powersum alien far-end crosstalk): A computation of signal coupling from multiple near-end disturbing channel pairs into a disturbed pair of a neighboring channel or part thereof, measured at the far-end.

Return Loss: A measure of the degree of impedance mismatch between two impedances. It is the ratio, expressed in decibels, of the amplitude of a reflected wave echo to the amplitude of the main wave at the junction of a transmission line and a terminating impedance.

Products. Technology.

Servi ces.

Delivered Globally

Propagation Delay: The time needed for the transmission of signal to travel the length of a single pair.

Delay Skew: The difference between the propagation delay of any two pairs within the same cable sheath. Delay skew is caused primarily because twisted pairs are designed to have different twists per foot (lay lengths). Delay skew could cause data transmitted over one channel to arrive out of sync with data over another channel.

Tests should also measure physical length of each link, and employ wire map to verify pin terminations at each end and identify simple electrical faults. Level Ile field test equipment accuracy is defined.

The following tables show the limitations for both the permanent links and channel

Category 3 Permanent Link					
Frequency (MHz)	Insertion Loss (dB)	NEXT (dB)			
1.0	3.5	40.1			
4.0	6.2	30.7			
8.0	8.9	25.9			
10.0	9.9	24.3			
16.0	13.0	21.0			

Category 3 Permanent Link Requirements

Category 3 Channel			
Frequency (MHz)	Insertion Loss (dB)	NEXT (dB)	
1.0	4.2	39.1	
4.0	7.3	29.3	
8.0	10.2	24.3	
10.0	11.5	22.7	
16.0	14.9	19.3	

Category 3 Channel Requirements

1.0	Loss (dB) 2.1	NEXT (dB) > 60	PSNEXT (dB) >57	ELFEXT (dB) 58.6	PSELFEXT (dB) 55.6	Return Loss (dB) 19.0
1.0	3.9	54.8	51.8	46.6	43.6	19.0
8.0	5.5	50.0	47.0	40.6	37.5	19.0
10.0	6.2	48.5	45.5	38.6	35.6	19.0
16.0	7.9	45.2	42.2	34.5	31.5	19.0
20.0	8.9	43.7	40.7	32.6	29.6	19.0
25.0	10.0	42.1	39.1	30.7	27.7	18.0
31.25	11.2	40.5	37.5	28.7	25.7	17.1
62.5	16.2	35.7	32.7	22.7	19.7	14.1
100.0	21.0	32.3	29.3	18.6	15.6	12.0

Category 5e Permanent Link Requirements

Maximum link propagation delay: 518 ns at 10 MHz Maximum link delay skew: 45 ns at 100 MHz

Category	5e Channel					
Frequency (MHz) 1.0	Insertion Loss (dB) 2.2	NEXT (dB) > 60	PSNEXT (dB) >57	ELFEXT (dB) 57.4	PSELFEXT (dB) 54.4	Return Loss (dB) 17.0
4.0	4.5	53.5	50.5	45.4	42.4	17.0
8.0	6.3	48.6	45.6	39.3	36.3	17.0
10.0	7.1	47.0	44.0	37.4	34.4	17.0
16.0	9.1	43.6	40.6	33.3	30.3	17.0
20.0	10.2	42.0	39.0	31.4	28.4	17.0
25.0	11.4	40.3	37.3	29.4	26.4	16.0
31.25	12.9	38.7	35.7	27.5	24.5	15.1
62.5	18.6	33.6	30.6	21.5	18.5	12.1
100.0	24.0	30.1	27.1	17.4	14.4	10.0

Category 5e Channel Requirements

Maximum channel propagation delay: 555 ns at 10 MHz Maximum channel delay skew: 50 ns at 100 MHz

TIA/EIA-568-B.2 Balanced Twisted Pair Cabling Components

100 ohm Unshielded Twisted Pair (UTP)

Horizontal Cable

As transmission rates have increased, higher performance UTP cabling has become a necessity. In addition, some means of classifying horizontal UTP cables and connecting hardware by performance capability had to be established. These capabilities have been broken down to a series of categories. The following categories are currently recognized:

Products. Technology.

Services. Delivered Globally

Category 3

Cables/connecting hardware with transmission parameters characterized up to 16 MHz

Category 5e

Cables/connecting hardware with transmission parameters characterized up to 100 MHz

Category 3 Horizontal and Backbone Cable (100 meters)						
Frequency (MHz) 0.772	Insertion Loss (dB) 2.2	NEXT (dB) 43.0	PSNEXT (dB) 43			
1.0	2.6	40.3	41			
4.0	5.6	32.3	32			
8.0	8.5	27.8	28			
10.0	9.7	26.3	26			
16.0	13.1	23.2	23			

Category 3 Horizontal and Backbone Cable

Maximum Cat 3 cable propagation delay: 545 ns/100 m at 10 MHz Maximum Cat 3 cable delay skew: 45 ns/100 m at 16 MHz

Category	5e Horizon	tal and Bac	kbone Cable	(100 m)		
Frequency (MHz) 0.772	Insertion Loss (dB) 1.8	NEXT* (dB) 67.0	PSNEXT (dB) 64.0	ELFEXT* (dB)	PSELFEXT (dB)	Return Loss (dB) 19.4
1.0	2.0	65.3	62.3	63.8	60.8	20.0
4.0	4.1	56.3	53.3	51.8	48.8	23.0
8.0	5.8	51.8	48.8	45.7	42.7	24.5
10.0	6.5	50.3	47.3	43.8	40.8	25.0
16.0	8.2	47.2	44.2	39.7	36.7	25.0
20.0	9.3	45.8	42.8	37.8	34.8	25.0
25.0	10.4	44.3	41.3	35.8	32.8	24.3
31.25	11.7	42.9	39.9	33.9	30.9	23.6
62.5	17.0	38.4	35.4	27.9	24.9	21.5
100.0	22.0	35.3	32.3	23.8	20.8	20.1

Category 5e Horizontal and Backbone Cable

call 1.800. Ani xter.

www. ani xter. com

visit

more information,

Maximum Cat 5e cable propagation delay: 538 ns/100 m at 100 MHz Maximum Cat 5e cable delay skew: 45 ns/100 m at 100 MHz

Characteristic impedance of horizontal cabling = 100 ohms \pm 15 percent from 1 MHz to the highest referenced frequency (16 or 100 MHz) of a particular category.

Bundled and Hybrid Cable

Bundled, wrapped or hybrid cables are allowed for use in horizontal cabling, provided that each individual cable type meets TIA/EIA-568-B.2 specifications and that powersum NEXT loss created by adjacent jacketed cables be 3 dB better than the normally allowed pair-to-pair NEXT for the cable type being tested. Color codes must follow individual cable standards to distinguish them from multipair UTP backbone cabling.

UTP Connecting Hardware

To ensure that installed connecting hardware (telecommunications outlets, patch cords and panels, connectors, cross-connect blocks, etc.) will have minimal effect on overall cabling system performance, the characteristics and performance parameters presented in this section must be met.

Category 3 Connecting Hardware								
Frequency (MHz)	Insertion Loss (dB)	NEXT (dB)						
1.0	0.1	58.0						
4.0	0.2	46.0						
8.0	0.3	39.9						
10.0	0.3	38.0						
16.0	0.4	33.9						

Category 3 Connecting Hardware

*Requirements for 25-pair cable are identical to those for 4-pair cable.

requency	Insertion	NEXT	FEXT	Return
(MHz)	Loss (dB)	(dB)	(dB)	Loss (dB)
1.0	0.1	65.0	65.0	30.0
4.0	0.1	65.0	63.1	30.0
8.0	0.1	64.9	57.0	30.0
10.0	0.1	63.0	55.1	30.0
20.0	0.2	57.0	49.1	30.0
25.0	0.2	55.0	47.1	30.0
31.25	0.2	53.1	45.2	30.0
62.5	0.3	47.1	39.2	24.1
100.0	0.4	43.0	35.1	20.0

Category 5e Connecting Hardware

The preferred termination method for all UTP connecting hardware includes the insulation displacement contact (IDC). To ensure overall system integrity, horizontal cables need to be terminated with connecting hardware of the same category or higher.

The following requirements apply only to wire and cable used for patch cords and cross-connect jumpers:

UTP Patch Cords

Jumper/Patch Cord Maximum Length Limitations:

- 20 m (66 ft) in main cross-connect
- 20 m (66 ft) in intermediate cross-connect
- 6 m (20 ft) in telecommunications room
- 3 m (10 ft) in the work area

Patch Cord Cable Construction:

- Stranded conductors for extended flex-life cables used for patch cords and cross-connect jumpers need to be of the same performance category (or higher) as the horizontal cables they connect.
- UTP cabling systems are not Category 3- or 5e-compliant unless all
 components of the system satisfy their respective category requirements.

Category 5e Assembled Patch Cords									
Frequency (MHz) 1.0	2 m Cord NEXT (dB) 65.0	5 m Cord NEXT (dB) 65.0	10 m Cord NEXT (dB) 65.0	Return Loss (dB) 19.8					
4.0	62.3	61.5	60.4	21.6					
8.0	56.4	55.6	54.7	22.5					
10.0	54.5	53.7	52.8	22.8					
16.0	50.4	49.8	48.9	23.4					
20.0	48.6	47.9	47.1	23.7					
25.0	46.7	46.0	45.3	24.0					
31.25	44.8	44.2	43.6	23.0					
62.5	39.0	38.5	38.1	20.0					
100.0	35.1	34.8	34.6	18.0					

Category 5e Assembled Patch Cords

Insertion Loss (Attenuation): per 100 m (328 feet) at 20 $^{\circ}$ C = horizontal UTP cable insertion loss + 20 percent (due to stranded conductors)

Services, Delivered Globally

TIA/EIA-568-B.2-1 Balanced Twisted Pair Cabling Components

Category 6 Transmission Performance

This addendum describes Category 6 cables, patch cords, connecting hardware, permanent link and channel transmission parameters characterized up to 250 MHz.

Matrix of Backward Compatible Mated Component Performance								
	Cat 3	Cat 5	Cat 5e	Cat 6				
Cat 3	Cat 3	Cat 3	Cat 3	Cat 3				
Cat 5	Cat 3	Cat 5	Cat 5	Cat 5				
Cat 5e	Cat 3	Cat 5	Cat 5e	Cat 5e				
Cat 6	Cat 3	Cat 5	Cat 5e	Cat 6				

Matrix of Backward Compatible Mated Component Performance

The lowest rated component determines the rating of the link or channel.

Category 6 Solid Horizontal and Backbone Cable									
Frequency (MHz) 0.772	Insertion Loss (dB) 1.8	NEXT* (dB) 76.0	PSNEXT (dB) 74.0	ELFEXT* (dB) 70.0	PSELFEXT (dB) 67.0	Return Loss (dB) 19.4			
1.0	2.0	74.3	72.3	67.8	64.8	20.0			
4.0	3.8	65.3	63.3	55.8	52.8	23.0			
8.0	5.3	60.8	58.8	49.7	46.7	24.5			
10.0	6.0	59.3	57.3	47.8	44.8	25.0			
16.0	7.6	56.2	54.2	43.7	40.7	25.0			
20.0	8.5	54.8	52.8	41.8	38.8	25.0			
25.0	9.5	53.3	51.3	39.8	36.8	24.3			
31.25	10.7	51.9	49.9	37.9	34.9	23.6			
62.5	15.4	47.4	45.4	31.9	28.9	21.5			
100.0	19.8	44.3	42.3	27.8	24.8	20.1			
200.0	29.0	39.8	37.8	21.8	18.8	18.0			
250.0	32.8	38.3	36.3	19.8	16.8	17.3			

Products. Technology. Services. Delivered Globally.

Category 6 Solid Horizontal and Backbone Cable (100 m)*

Maximum Cat 6 cable propagation delay: 538 ns/100 m at 100 MHz (536 at 250 MHz)

Maximum Cat 6 cable delay skew: 45 ns/100 m at all frequencies The PSNEXT performance of bundled or hybrid cables must be 1.2 dB greater than shown above.

^{*}Horizontal and backbone cables are defined only as identical 4-pair cables.

Category 6	Connecting Hard	lware			
Frequency (MHz) 1.0	Insertion Loss (dB) 0.10	NEXT (dB) 75.0	FEXT (dB) 75.0	Return Loss (dB) 30.0	
4.0	0.10	75.0	71.1	30.0	
8.0	0.10	75.0	65.0	30.0	
10.0	0.10	74.0	63.1	30.0	
16.0	0.10	69.9	59.0	30.0	
20.0	0.10	68.0	57.1	30.0	
25.0	0.10	66.0	55.1	30.0	
31.25	0.11	64.1	53.2	30.0	
62.5	0.16	58.1	47.2	28.1	
100.0	0.20	54.0	43.1	24.0	
200.0	0.28	48.0	37.1	18.0	
250.0	0.32	46.0	35.1	16.0	

Category 6 Connecting Hardware

For more information, visit www. anixter.com or call 1.800. Anixter.

Category 6	Assembled Patch	Cords		
Frequency (MHz) .772	2 m Cord NEXT (dB) 65.0	5 m Cord NEXT (dB) 65.0	10 m Cord NEXT (dB) 65.0	Return Loss (dB) 19.4
1.0	65.0	65.0	65.0	19.8
4.0	65.0	65.0	65.0	21.6
8.0	65.0	65.0	64.8	22.5
10.0	65.0	64.5	62.9	22.8
16.0	62.0	60.5	59.0	23.4
20.0	60.1	59.6	57.2	23.7
25.0	58.1	56.8	55.4	24.0
31.25	56.2	54-9	53.6	23.0
62.5	50.4	49.2	48.1	20.0
100.0	46.4	45.3	44.4	18.0
125.0	44.5	43.5	42.7	17.0
150.0	43.0	42.1	41.4	16.2
175.0	41.8	40.9	40.2	15.6
200.0	40.6	39.8	39.3	15.0
225.0	39.7	38.9	38.4	14.5
250.0	38.8	38.1	37.6	14.0

Category 6 Assembled Patch Cords

Insertion loss (attenuation) per 100 m (328 ft at 20°C) is defined as equal to UTP solid cable insertion loss plus 20 percent. (The increased insertion loss allowance is due to stranded conductors.)

Insertion

Loss (dB)

1.9

3.5

5.0

5.5

7.0

7.9

8.9

10.0

144

18.6

27.4

10.0

16.0

20.0

25.0

31.25

62.5

100.0

200.0

250.0

NFXT*

(dB)

65.0

64.1

59 4

57.8

54.6

53.1

50.0

45.1

41.8

36.9

35.3

PSNFXT

(dB)

62.0

61.8

57.0

55.5

52.2

50.7

49.1

47.5

42.7

39.3

34.3

32.7

FI FFXT*

(dB)

64.2

52.1

461

44.2

40.1

38.2

36.2

34.3

28.3

24.2

18.2

16.2

PSELFEXT

(dB)

61.2

49.1

43.1

41.2

37.1

35.2

33.2

31.3

25.3

21.2

15.2

Return

Loss (dB)

19.1

21.0

21.0

21.0

20.0

19.5

19.0

18.5

16.0

14.0

11.0

10.0

call 1.800. Ani xter.

or

www. ani xter. com

visit

more information,

Category 6 Channel									
Frequency (MHz) 1.0	Insertion Loss (dB) 2.1	NEXT* (dB) 65.0	PSNEXT (dB) 62.0	ELFEXT* (dB) 63.3	PSELFEXT (dB) 60.3	Return Loss (dB) 19.0			
4.0	4.0	63.0	60.5	51.2	48.2	19.0			
8.0	5.7	58.2	55.6	45.2	42.2	19.0			
10.0	6.3	56.6	54.0	43.3	40.3	19.0			
16.0	8.0	53.2	50.6	39.2	36.2	18.0			
20.0	9.0	51.6	49.0	37.2	34.2	17.5			
25.0	10.1	50.0	47.3	35.3	32.3	17.0			
31.25	11.4	48.4	45.7	33.4	30.4	16.5			
62.5	16.5	43.4	40.6	27.3	24.3	14.0			
100.0	21.3	39.9	37.1	23.3	20.3	12.0			
200.0	31.5	34.8	31.9	17.2	14.2	9.0			
250.0	35.9	33.1	30.2	15.3	12.3	8.0			

Category 6 Channel

Maximum Cat 6 channel propagation delay: less than 555 ns at 10 MHz Maximum Cat 6 channel delay skew: less than 50 ns/100m at 10 MHz

Category 6 Longito	udinal Conversion Loss (LCL	
Frequency (MHz) 1.0	Cable LCL (dB) 40.0	Connector LCL (dB) 40.0
4.0	40.0	40.0
8.0	40.0	40.0
10.0	40.0	40.0
16.0	38.0	40.0
20.0	37.0	40.0
25.0	36.0	40.0
31.25	35.1	38.1
62.5	32.0	32.1
100.0	30.0	28.0
200.0	27.0	22.0
250.0	26.0	20.0

Category 6 Longitudinal Conversion Loss (LCL)

Longitudinal Conversion Transfer Loss (LCTL) is not yet defined.

TIA Category 6 versus Augmented Category 6									
	TIA Category 5e UTP	TIA Category 6 UTP	TIA Augmented Category 6 UTP	ISO Class E _A					
Recognized by IEEE 802.3an	No	Yes	Yes	Yes					
55 Meter Distance Support	No	Yes	Yes	Yes					
100 Meter Distance Support	No	No	Yes	Yes					
Extrapolated Test Limits for NEXT and PSNEXT									
to 500MHz	No	No	No	Yes					

Note: This table compares current TIA Category 6 cabling with new TIA and ISO specifications for 10 Gigabit cabling. This table summarizes the various UTP cabling options and their respective 10 Gigabit performance attributes as defined by the latest draft standards. Category 5e is not recognized as a viable cabling media to support 10 Gigabit transmission regardless of its installed cabling distance. Category 6 cabling will only support 10 Gigabit at a maximum installed distance of 55 meters.

TIA/EIA-568-B.2-Addendum 10 Balanced Twisted Pair Cabling Components (Augmented Category 6)

Augmented Category 6 Transmission Performance
This addendum describes Augmented Category 6 cables, patch cords,
connecting hardware, permanent link and channel transmission parameters
characterized up to 500 MHz. (Please note: this addendum is in draft
form at the time of this publication. This information does not reflect
the final published standard).

Augme	Augmented Category 6 Permanent Link Requirements									
Frequency MHz) 1.0	y Insertion Loss (dB) 1.9	NEXT (dB) 65.0	PSNEXT (dB) 62.0	ACR-F (dB) 64.2	PSACR-F (dB) 61.2	Return Loss (dB) 19.1	PSANEXT (dB) 67.0	PSAACRF (dB) 67.0		
4.0	3.5	64.1	61.8	52.1	49.1	21.0	67.0	65.7		
8.0	4.9	59.4	57.0	46.1	43.1	21.0	67.0	59.6		
10.0	5.5	57.8	55.5	44.2	41.2	21.0	67.0	57.7		
16.0	6.9	54.6	52.2	40.1	37.1	20.0	67.0	53.6		
20.0	7.7	53.1	50.7	38.2	35.2	19.5	67.0	51.7		
25.0	8.7	51.5	49.1	36.2	33.2	19.0	67.0	49.7		
31.25	9.7	50.0	47.5	34.3	31.3	18.5	66.2	47.8		
62.50	13.9	45.1	42.7	28.3	25.3	16.0	63.1	41.8		
100.0	17.9	41.8	39.3	24.2	21.2	14.0	61.1	37.8		
200.0	26.0	36.9	34.3	18.2	15.2	11.0	56.6	31.8		
250.0	29.4	35.3	32.7	16.2	13.2	10.0	55.5	29.8		
300.0	32.6	34.0	31.4	14.6	11.6	9.2	53.9	28.2		
400.0	38.4	29.9	27.1	12.1	9.1	8.0	52.1	25.7		
500.0	43.8	26.7	23.8	10.2	7.2	8.0	50.6	23.7		

Augmented Category 6 Permanent Link Requirements

Augmen	ited Categ	ory 6 Chai	nnel Requi	irement				
Frequency MHz) 1.0	Insertion Loss (dB) 2.2	NEXT (dB) 65.0	PSNEXT (dB) 62.0	ACR-F (dB) 63.3	PSACR-F (dB) 60.3	Return Loss (dB) 19.0	PSANEXT (dB) 67.0	PSAACRF (dB) 67.0
4.0	4.1	63.0	60.5	51.2	48.2	19.0	67.0	65.0
8.0	5.7	58.2	55.6	45.2	42.2	19.0	67.0	58.9
10.0	6.4	56.6	54.0	43.3	40.3	19.0	67.0	57.0
16.0	8.1	53.2	50.6	39.2	36.2	18.0	67.0	52.9
20.0	9.1	51.6	49.0	37.2	34.2	17.5	67.0	51.0
25.0	10.2	50.0	47.3	35.3	32.3	17.0	66.0	49.0
31.25	11.4	48.4	45.7	33.4	30.4	16.5	65.1	47.1
62.50	16.3	43.4	40.6	27.3	24.3	14.0	62.0	41.1
100.0	20.8	39.9	37.1	23.3	20.3	12.0	60.0	37.0
200.0	30.0	34.8	31.9	17.2	14.2	9.0	55.5	31.0
250.0	33.8	33.1	30.2	15.3	12.3	8.0	54.0	29.0
300.0	37.3	31.7	28.8	13.7	10.7	7.2	52.8	27.5
400.0	43.6	28.7	25.8	11.2	8.2	6.0	51.0	25.0
500.0	49.3	26.1	23.2	9.3	6.3	6.0	49.5	23.0

Services. Delivered Globally

Augmented Category 6 Channel Requirement

Note: The draft requirements for ISO (The International Organization for Standardization) 11801 Class E_A are more demanding compared to TIA/EIA Augmented Cat 6 draft requirements. Anixter's Enterprise Cabling Lab tests to the more stringent ISO 11801 draft standards.

ISO Compared to TIA		
Characteristics 500MHz (dB) PSNEXT LOSS	ISO Class E _A 24.8dB	TIA Augmented Cat 6 Draft 23.2dB
NEXT Loss	27.9dB	26.1dB
PSANEXT Loss	49.5dB	49.5dB
Return Loss	8.0dB	6.0dB
Insertion Loss	49.3dB	49.3dB
Referred to by IEEE	Yes	No

Note: See the IEEE 802.3an and ISO Class EA section of this book for more information on 10 Gigabit cabling and protocol methods.

TIA/EIA-568-B.3 Optical Fiber Cabling Components

Optical Fiber Cabling Systems

Optical Fiber Cabling Media

- Horizontal 62.5/125 or 50/125 µm multimode optical fiber (minimum of two fibers)
- Backbone 62.5/125 or 50/125 μ m multimode or single-mode optical fiber

Cable Transmission Performance Parameters Multimode (Horizontal and Backbone)

Wavelength (nm) 850	Maximum Attenuation (dB/km) 3.5	50 µm Minimum Bandwidth (MHz/km) 500	62.5 µm Minimum Bandwidth (MHz/km) 160
1,300	1.5	500	500

Cable Transmission Performance Parameters Single-mode (Backbone)

Wavelength	Inside Plant Maximum Attenuation	Outside Plant Maximum Attenuation
(nm) 1,310	(dB/km) 1.0	(dB/km) 0.5
1,550	1.0	0.5

Optical Fiber Bend Radius	
Fiber Type	Bend Radius
Small Inside Plant Cable (2–4 fibers)	1" (no load)
	2" (with load)
All Other Inside Plant Cable	10 x diameter (no load)
	15 x diameter (with load)
Outside Plant Cable	10 x diameter (no load)
	20 x diameter (with load)

Outside plant cable must be water-blocked and have a minimum pull strength of 600 lbs. (Drop cable pull strength may be 300 lbs.)

Optical Fiber Connector

No specified connector: 568SC and other duplex designs may be used.

Color Identification

- Beige multimode connector/coupling
- Blue single-mode connector/coupling

Note: The ISO/IEC standard now specifies the 568SC-type fiber connector in the work area.

Optical Fiber Telecommunications Outlet

Required Features

 Capability to terminate minimum of two fibers into 568SC couplings or other duplex connection Technol ogy.

Delivered Globally

 Means of securing fiber and maintaining minimum bend radius of 25 mm (1")

Optical Fiber Splices, Fusion or Mechanical

- Maximum insertion loss 0.3 dB
- Minimum return loss:
 - Multimode: 20dB
 - Single-mode: 26dB
 - Single-mode: 55dB (analog CATV)

Optical Fiber Connector (mated pair)

Maximum insertion loss 0.75 dB

Patch Cords

- Shall be dual fiber of the same type as the horizontal and backbone fiber
- Polarity shall be keyed duplex

Purpose of the ANSI/TIA/EIA-569-B Standard

intelligent building controls over media that includes fiber optics, specialized copper data cabling, microwave and radiowave. This booklet concisely years. Software, hardware and communications gear have far shorter structured cabling plant, capable of running any voice or data application

Section Contents

ANSI/TIA/FIA-569-B

Commercial Building Standard for Telecommunications Pathways and Spaces

Design Considerations	
Entrance Facilities	
Service Entrance Pathways	
Equipment Room	
ntrabuilding Backbone Pathways	
Telecommunications Room	
Horizontal Pathways	
Underfloor Duct	
Flushduct	
Multi-channel Raceway	
Cellular Floor	
Trenchduct	
Access Floor	
Plenum/Ceiling44	
Conduit	
Cable Trays	
Perimeter Pathways45	
Consolidation Points and MUTOAs47	
Electromagnetic Interference	
Tractors 10	

Standards Reference Guide

Pathways and Spaces


1. 800. Ani xter.

or

www. ani xter. com

visit

For more information,



1. Electric Entrance	5. Voice
2. Telco Entrance	6. Telecommunications Room
3. Telecommunications Equipment Room	7. Grounding and Bonding
4. Data	8. Underfloor System

TIA/EIA-569-B Design Considerations

Entrance Facilities

Entrance facilities include the pathways for outside carrier services, interbuilding backbone, alternate entrance and antennae entrance pathways. The entrance facilities consist of a termination field interfacing any outside cabling to the intrabuilding backbone cabling. The local telephone carrier is typically required to terminate cabling within 50 ft of building penetration and to provide primary voltage protection.

In buildings larger than 20,000 usable sq. ft., a locked, dedicated, enclosed room is recommended. Beyond 70,000 sq. ft., a locked, dedicated room is required, with a plywood termination field provided on two walls. In buildings up to 100,000 usable sq. ft., a wall-mounted termination field may serve as the entrance facility, using 3/4-inch plywood, 8 ft high. Beyond 100,000 sq. ft., rack-mounted and free-standing frames may also be required. Minimum space requirements are given as follows:

Service Entrance Pathways

For underground facilities, use a minimum 4-inch conduit or duct constructed of PVC type B, C or D, multiple plastic duct, galvanized steel, or fiber glass with appropriate encasement. No more than two 90° manufactured bends are allowed (10 times the diameter). Drain slope should not be less than 12 inches per 100 ft. Recommended conduit fill varies but should not exceed 40 percent for more than two cables.

Maintenance holes (typically 3,500 lb./sq. in., concrete) must be equipped with sump, corrosion-protected pulling iron, cable racks, grounded ladder and only such power and light conductors as required for telecommunications support per NEC requirements.

Gross Building Floor Space (sq. ft. / sq. m.)	Plywood Field		Room Dimension	
5,000/465	8' high x 39" wide	(3m x 99cm)		
10,000/1,000	8' high x 39"	(3m x 99cm)		
20,000/2,000	8' high x 42"	(3m x 107cm)	(A room recomm	ended
40,000/4,000	8' high x 68"	(3m x 173cm)	beyond this leve	1)
50,000/5,000	8' high x 90"	(3m x 229cm)		
60,000/6,000	8' high x 96"	(3m x 244cm)	(A dedicated roo	m required)
80,000/8,000	8' high x 120"	(3m x 305cm)	12' x 6.3'	(4m x 2m)
100,000/10,000	8' high x 2 walls	(3m x 2 walls)	12' x 6.3'	(4m x 2m)
200,000/20,000	8' high x 2 walls	(3m x 2 walls)	12' x 9'	(4m x 3m)
400,000/40,000	8' high x 2 walls	(3m x 2 walls)	12' x 13'	(4m x 4m)
500,000/50,000	8' high x 2 walls	(3m x 2 walls)	12' x 15.6'	(4m x 5m)
600,000/60,000	8' high x 2 walls	(3m x 2 walls)	12' x 18.3'	(4m x 6m)
800,000/80,000	8' high x 2 walls	(3m x 2 walls)	12' x 22.3'	(4m x 7m)
1,000,000/100,000	8' high x 2 walls	(3m x 2 walls)	12' x 27.7'	(4m x 9m)

Rule of thumb: Allow 1 sq. ft. (929 sq. centimeter) of plywood wallmount for each 200 sq. ft. (19 sq. meter) area of floor space.

Equipment Room

An equipment room is essentially a large telecommunications room that may house the main distribution frame, PBXs, secondary voltage protection, etc. The equipment room is often appended to the entrance facilities or a computer room to allow shared air conditioning, security, fire control, lighting and limited access.

Number of	Equipment Room
Workstations	Floor Space (sq. ft.)
1–100	150 (14 sq. meters)
101-400	400 (38 sq. meters)
401-800	800 (74 sq. meters)
801-1,200	1,200 (111 sq. meters)

Rule of thumb: Provide 0.75 sq. ft. (697 sq. centimeter) of equipment room floor space for every 100 sq. ft. (9 sq. meter) of user workstation area.

Location

Typically, rooms should be located away from sources of electromagnetic interference (transformers, motors, x-ray, induction heaters, arc welders, radio and radar).

Perimeters

Typically, no false ceiling; all surfaces treated to reduce dust; walls and ceiling painted white or pastel to improve visibility.

Limited Access

Typically, single or double 36" x 80" lockable doors with no doorsills.

Other

Typically, no piping, ductwork, mechanical equipment or power cabling should be allowed to pass through the equipment room. No unrelated storage.

Technol ogy.

Servi ces.

Delivered Globally

Ceiling Height

Minimum clear height in room shall be 8 ft. (2.4 m), the height between the finished floor and the lowest point should be 10 ft. (3 m) to accommodate tall racks and overhead raceways. False ceilings should not be installed.

HVAC

24 hours a day, 365 days a year, 64° to 75° F, 30 to 55 percent humidity, positive pressure, with independent power from telecommunications equipment.

Lighting

Typically, 8.5 ft. high, providing 50 ft. candles at 3 ft. above floor.

Electrical

Typically, a minimum of two dedicated 15 A, 110 V AC duplex outlets on separate circuits is required. Convenience duplex outlets shall be placed at 6 ft. intervals around the perimeter. Emergency power should be considered and supplied if available.

Bonding and Grounding

Access shall be available to the bonding and grounding as specified in J-STD-607-A.


Dust

Less than 100 micrograms/cubic meter/24 hour period.

Note: The term "typically" is applied here to indicate, where applicable, that these requirements also apply to other elements of the cabling system spaces. Lighting requirements, for instance, are largely identical for entrance facilities, equipment rooms and telecommunication rooms.

Intrabuilding Backbone Pathways

Within a building, the intrabuilding backbone pathways extend between the entrance facilities, equipment room and telecommunications rooms. Telecommunication rooms should be stacked vertically above each other on each floor, and provided with a minimum of three 4-inch sleeves (a stub of conduit through the floor) for less than 50,000 sq. ft. served. An equivalent 4" x 12" slot may be used in lieu of three sleeves. Firestopping is required. If rooms are not vertically aligned, then 4-inch horizontal conduit runs are required. Include no more than two 90° bends between pull points. Pulling iron or eyes embedded in the concrete for cable pulling is recommended. Fill should not exceed 40 percent for any run greater than two cables.



Backbone and Horizontal Pathways


1. Telco Conduit	6. Vertical Backbone
2. Telco Manhole	7. Telecommunications Room
3. Entrance Conduit	8. Horizontal Cabling
4. Telco Entrance Facility	9. Interbuilding Backbone
5. Telecommunications Equipment Room	10. Flectrical Entrance Facility

Telecommunications Room


The telecommunications room on each floor is the junction between backbone and horizontal pathways. It contains active voice and data telecommunications equipment, termination fields and cross-connect wiring. More than one telecommunications room per floor is required if distance to a work area exceeds 300 feet, or if floor area served exceeds 10,000 square feet. Recommended room sizing is 10' x 11' for each 10,000 square-foot area served. Power, lighting, air conditioning and limited access are typical. See requirements for equipment room. There are a minimum of three 4-inch firestopped backbone sleeves in the floor at the left side of a plywood termination field, which are ideally located near the door. A fire extinguisher is recommended.

Technol ogy.

Services, Delivered Globally



Riser Sleeve



Typical Telecommunications Room

Horizontal Pathways

Horizontal pathways extend between the telecommunications room and the work area. A variety of generic pathway options are described. Choice of pathway(s) is left to the discretion of the designer. The most commonly employed pathway consists of cable bundles run from the telecommunications room along J-hooks suspended above a plenum ceiling, which fan out once a work zone is reached. They then drop through interior walls or support columns or raceways, and terminate at an information outlet (I/O).

Other options include the following:

Underfloor Duct

Single - or dual-level rectangular ducts imbedded in greater than 2.5-inch (7 cm) concrete flooring.

Flushduct

Single-level rectangular duct imbedded flush in greater than 1-inch (3 cm) concrete flooring.

Multi-channel Raceway

Cellular raceway ducts capable of routing telecommunications and power cabling separately in greater than 3-inch (8 cm) reinforced concrete.

Cellular Floor

Pre-formed hollows or steel-lined cells are provided in concrete with header ducts from the telecommunications room arranged at right angles to the cells.

Trenchduct

A wide, solid tray, sometimes containing compartments, and fitted with a flat top (with gaskets) along its entire length. It is embedded flush with the concrete finish

Access Floor

Modular floor panels supported by pedestals, used in computer rooms and equipment rooms.

Plenum/Ceiling

Bundled cables, suspended above a false ceiling, fan out to drop through walls, power poles or along support columns to baseboard level.

Conduit

To be considered only when outlet locations are permanent, device density low and flexibility (future changes) are not required.

Cable Trays

Options include channel tray, ladder tray, solid bottom, ventilated and wireway.

Technol ogy.


Servi ces.

Delivered Globally

Perimeter Pathways

Options include surface raceway, recessed, molding and multichannel (to carry separate power and lighting circuits).


Rule of thumb: Typically, size horizontal pathways by providing 1 sq. in. of cross-section area for every 100 sq. ft. of workspace area being served.



Perimeter Pathway and Modular Office Path

Note: Typically, a pull box, splice box or pulling point is required for any constrained pathway where there are more than two 90° bends, a 180° reverse bend or length more than 100 ft.

A Variety of Horizontal Pathways



Access Floor


call 1.800. Ani xter

or


www. ani xter. com

visit

more information,



Access Floor



Ceiling Utility Pole

Consolidation Points and MUTOAs

Consolidation points provide limited area connection access. Typically, a permanent flush wall, ceiling or support column-mounted panel serves modular furniture work areas. The panels must be unobstructed and fully accessible without moving fixtures, equipment or heavy furniture.

A Multi-User Telecommunication Outlet Assembly (MUTOA) is another methodology to reduce cabling moves, adds and changes in modular furniture settings. The user cord is directly connected to the MUTOA. A MUTOA location must be accessible and permanent, and may not be mounted in ceiling spaces or under access flooring. Similarly, it cannot be mounted in furniture unless that furniture is permanently secured to the building structure.

For more descriptive information on distance limitations and purposes of consolidation points and MUTOAs, see ANSI/TIA/EIA-568-B.1.


Electromagnetic Interference

Voice and data telecommunications cabling should not be run adjacent and parallel to power cabling — even along short distances — unless one or both cable types are shielded and grounded. For low voltage communication cables, a minimum 5-inch distance is required from any fluorescent lighting fixture or power line over 2 kVA and up to 24 inches from any power line over 5 kVA*. In general, telecommunications cabling is routed separately, or several feet away from power cabling. Similarly, telecommunications cabling is routed away from large motors, generators, induction heaters, arc welders, x-ray equipment and radio frequency, microwave or radar sources.

*Note: Distance recommendations from (1990) TIA/EIA-569 are reproduced here by popular request. For current recommendations, refer to NEC/NEPA 70. Article 800-52

Firestops

Annex A of the standard discusses various types of packing used to re-establish the integrity of fire-rated structures when these barriers have been penetrated by cable. This section of the standard briefly discusses passive mechanical systems and non-mechanical systems such as putty, caulk, cements, intumescent sheets and strips, silicone foams and pre-manufactured pillows. The most common method is stuffing all apertures with ceramic/mineral wool and caulking both sides with fire-resistant putty. The information refers the designer to check manufacturer specifications and UL ratings against NFPA, ASTM and NEC codes.



Cut-a-Way of Typical Firestop

Purpose of the ANSI/TIA/EIA-606-A Standard

Modern buildings require an effective telecommunications infrastructure to support the wide variety of services that rely on the electronic transport of information. Administration includes basic documentation and timely updating of drawings, labels and records. Administration should be synergistic with voice, data and video telecommunications, as well as with other building signal systems, including security, audio, alarms and energy management. Administration can be accomplished with paper records, but in today's increasingly complex telecommunications environment, effective administration is enhanced by the use of computer-based systems. A multi-tenant commercial building has a life expectancy of at least 50 years. Moreover, in a multi-tenant environment, continuous moves, adds and changes are inevitable.

Administrative recordkeeping plays an increasingly necessary role in the flexibility and management of frequent moves, adds and changes. This booklet concisely describes the administrative recordkeeping elements of a modern structured cabling system.

Section Contents

TIA/FIA-606-A

Administration Standard for Commercial Telecommunications Infrastructure

Elements of an Administration System
Classes of Administration
Class 1 Administration
Class 2 Administration
Class 3 Administration
Class 4 Administration
Identification Formats
Summary of Record Elements5
Grounding/Bonding Administration5
Label Color Coding


TIA/EIA-606-A

Administration Standard for Commercial Telecommunications Infrastructure

Elements of an Administration System:

- · Horizontal pathways and cabling
- Backbone pathways and cabling
- Telecommunications grounding/bonding
- Spaces (e.g. entrance facility, telecommunications room, equipment room)
- Firestopping

The figure below illustrates a typical model for the infrastructure elements used in an administration system:



Technol ogy.

Servi ces.

Delivered Globally

Classes of Administration

Four classes of administration are specified in this standard to accommodate diverse degrees of complexity present in telecommunications infrastructure. Each class defines the administration requirements for identifiers, records and labeling. An administration system can be managed using a paper-based system, general-purpose spreadsheet software, or special-purpose cable management software.

Identifier	Description of Identifier	Class of	Ad	mini	stration
fs	Telecommunications Space (TS)	R	R	R	R
fs-an	Horizontal link	R	R	R	R
fs-TGMB	Telecommunications Main Grounding Busbar (TMGB)	R	R	R	R
fs-TGB	Telecommunications Grounding Busbar (TGB)	R	R	R	R
fs ₁ /fs ₂ -n	Building backbone cabling		R	R	R
fs ₁ /fs ₂ -n.d	Building backbone pair or optical fiber		R	R	R
f-FSLn(h)	Firestop location		R	R	R
[b ₁ -fs ₁]/[b ₂ -fs ₂]-n	Campus backbone cable			R	R
[b ₁ -fs ₁]/[b ₂ -fs ₂]-n/d	Campus backbone or optical fiber			R	R
b	Building			R	R
С	Campus or site				R

Class 1 Administration

Class 1 addresses the administration requirements for a building or premise that is served by a single Equipment Room (ER).

The following infrastructure identifiers shall be required in Class 1 Administration when the corresponding elements are present:

Technol ogy.

Servi ces.

Delivered Globally

- Telecommunications Space (TS) identifier
- Horizontal Link identifier
- Telecommunications Main Grounding Busbar (TMGB)
- Telecommunications Grounding Busbar (TGB)

Class 1 Identifiers f = numeric character (s) identifying the floor of the building occupied by the TS s = alpha character (s) uniquely identifying the TS on floor f, or the building area in which the space is located fs = the TS identifier a = one or two alpha characters uniquely identifying a single patch panel, a group of patch panels with sequentially numbered ports, or an IDC connector (punch down block), or a group of IDC connectors, serving as part of the horizontal cross-connect

or the section of an IDC connector on which a four-pair horizontal cable is terminated in the TS

TMGB = portion of an identifier designating a telecommunications main grounding busbar

TGB = portion of an identifier designating a telecommunications grounding busbar

n = two to four numeric characters designating the port on a patch panel,

Class 2 Administration

Class 2 addresses the administration of infrastructure with one or more Telecommunications Spaces (TS) in a single building.

The following infrastructure identifiers shall be required in Class 2 Administration when the corresponding elements are present:

- Identifiers required in Class 1 Administration
- · Building backbone cable identifier
- · Building backbone pair or optical fiber identifier
- · Firestopping location identifier

Class 2 Administration may additionally include pathway identifiers.

Class 2 Identifiers

- $\mathsf{fs_1} = \mathsf{IS}$ identifier for the space containing the termination of one end of the backbone cable
- ${\rm fs_2}={\rm TS}$ identifier for the space containing the termination of the other end of the backbone cable
- n = one or two alpha-numeric characters identifying a single cable with one end terminated in the TS designated fs1 and the other end terminated in the TS designated FS2
- fs_1/fs_2 -n = a building backbone cable identifier
 - $d=\mbox{two}$ to four numeric characters identifying a single copper pair or a single optical fiber
 - FSL = an identifier referring to a firestopping location
 - h = one numeric character specifying the hour rating of a firestopping system

Class 3 Administration

Class 3 Administration addresses infrastructure with multiple buildings at a single site.

The following infrastructure identifiers shall be required in Class 3 Administration:

Technol ogy.

Servi ces.

Delivered Globally

- Identifiers required in Class 2 Administration
- · Building identifier
- · Campus backbone cable identifier
- Campus backbone pair or optical fiber identifier

The following infrastructure identifiers are optional in Class 3 Administration:

- Identifiers optional in Class 2 Administration
- Outside plant pathway element identifier
- · Campus pathway or element identifier

Additional identifiers may be added if desired.

Class 2 Identifier

 $[b_1-fs_1]/[b_2-fs_2]-n = Campus backbone identifier$

d = two to four numeric characters identifying a single copper pair or a single optical fiber

b = one or more alpha numeric characters identifying a single building

Class 4 Administration

Class 4 Administration addresses infrastructure with multiple sites or campuses.

The following infrastructure identifiers shall be required in Class 4 Administration:

- Identifiers required in Class 3 Administration
- · Campus or site identifier

The following infrastructure identifiers are optional in Class 4 Administration:

- Identifiers optional in Class 3 Administration
- Inter-campus lement identifier

Additional identifiers may be added if desired.

Class 4 Identifiers

 $\ensuremath{\mathtt{c}} = \ensuremath{\mathtt{one}}$ or more alpha-numeric characters identifying a campus or a site

Identification Formats

A unique alphanumeric identification code is created for every location, pathway, cable and termination point. Suggestions in the standard include:

Technol ogy.

Delivered Globally.

Alphanumeric Identification Code				
BCxxx	bonding conductor	ННххх	handhole	
BCDxxx	backbone conduit	ICxxx	intermediate cross-connect	
Сххх	cable	Jxxx	jack	
СВххх	backbone cable	MCxxx	main cross-connect	
CDxxx	conduit	MHxxx	manhole or maintenance hole	
CTxxx	cable tray	РВххх	pull box	
ECxxx	equipment (bonding) conductor	Sxxx	splice	
EFxxx	entrance facility	SExxx	service entrance	
ERxxx	equipment room	SLxxx	sleeve	
Fxxx	fiber	TCxxx	telecommunications closet	
GBxxx	grounding busbar	TGBxxx	telecommunications grounding busbar	
GCxxx	grounding conductor	TMGB	telecommunications main grounding busbar	
		WAxxx	work area	

Identification Format Example

The actual format in the preceding chart is not mandated by the standard. However, the chosen format must be consistent and provide a unique identifier number for each system element. This method lends itself to organization and updating of multiple records by the use of powerful relational database (three-dimensional spreadsheet) programs.

Identification Example

J0001	Label for an information outlet jack
D306	Designation for a work area

3A-C17-005 Termination in closet 3A, column C, row 17, block position 005

Examples like those above (taken from the TIA/EIA 606-A text and administrative labeling map) indicate the flexibility of conventions that can be established for purposes of naming. Logical naming conventions can also convey considerable additional information about other linkages. Further examples are included in the complete standard.

This table outlines the minimum required information and required linkages. Further information is optional. A multidimensional database or spreadsheet is helpful.

	Record	Required Information	Required Linkages
	Pathway	Pathway Identification #	Cable Records
		Pathway Type	Space Records
Pathways		Pathway Fill	Pathway Records
&		Pathway Load	Grounding Records
Spaces	Space	Space Identification #	Pathway Records
эриссэ	эрисс	Space Type	Cable Records
		эрасс турс	Grounding Records
	Cable	Cable Identification #	Termination Records
	Caulc	Cable Type	Splice Records
		Unterminated Pair #s	Pathway Records
		Damaged Pair #s	Grounding Records
		Available Pair #s	Grounding Records
	Termination	Available Pall #S Termination Hardware #s	Termination Position Records
Milledon			
Wiring	Hardware	Termination Hardware Type	Space Records
	Tourston	Damaged Position #s	Grounding Records
	Termination	Termination Position #	Cable Records
	Position	Termination Position Type	Other Termination Records
		User Code	Termination Hardware Records
		Cable Pair/Condition #s	Space Records
	Splice	Splice Identification #	Cable Records
		Splice Type	Space Records
	TMGB	TMGB Identification #	Bonding Conductor Records
		Busbar Type	Space Records
		Grounding Conductor #s	
		Resistance to Earth	
		Date of Measurement	
Grounding	Bonding	Bonding Conductor ID#	Grounding Busbar Records
		Conductor Type	Pathway Records
	Conductor	Busbar Identification #	
	TGB	Busbar Identification #	Bonding Conductor Records
		Busbar Type	Space Records

Grounding/Bonding Administration

Telecommunications systems require a reliable electrical ground reference potential, provided by a dedicated grounding/bonding conductor network.

WARNING

IF THIS CLAMP OR CABLE IS LOOSE OR MUST BE REMOVED, PLEASE CALL THE BUILDING TELECOMMUNICATIONS MANAGER

Technology. Services.

Delivered Globally.

Bonding conductor cabling shall be colored green or labeled appropriately with an alphanumeric identifier and warning label. Grounding records are similar to cable record format.

Grounding/Bonding Terms (with acronyms):

TMGB Telecommunications Main Grounding Busbar
TBB Telecommunications Bonding Backbone
TGB Telecommunications Grounding Busbar
TBBIBC Telecommunications Bonding Backbone
Interconnecting Bonding Conductor

Label Color Coding

Shown here are the color codes used for termination field labels.

ermination Type	Color	Comments
Demarcation Point	Orange	CO terminations
Network Connections	Green	also aux. circuit terms.
Common Equipment	Purple	PBX, Host, LANs, Mux
First-level Backbone	White	MC-IC terminations
Second-level Backbone	Gray	IC-TC terminations
Station	Blue	Horizontal cable terms.
Interbuilding Backbone	Brown	Campus cable terms.
Miscellaneous	Yellow	Aux., maint., security
Key Telephone Systems	Red	

The abbreviation "term(s)." is used in this example (for space considerations) to mean "termination(s)."

61

The Purpose of J-STD-607-A

This standard specifies a uniform telecommunications grounding and bonding infrastructure that shall be followed within commercial buildings. Following the AT&T divestiture of 1984, the end user became responsible for all premises cabling for voice and data. Advancements in voice communications and the convergence of voice and data communications led to increasingly complex interactive systems owned and maintained by the end user. These systems require a reliable electrical ground-reference potential. Grounding by attachment to the nearest piece of iron pipe is no longer satisfactory to provide ground-reference for sophisticated active electronics systems

Section Contents

J-STD-607-A

Commercial Building Grounding and Bonding Requirements for Telecommunications

ign Considerations \ldots 6	2
ns	2
ematic Diagram &	3


Solid copper grounding busbars (1/4" thick x 4" high x variable length) are installed with insulated standoffs in entrance facilities and the equipment room, as well as each telecommunications room (1/4" thick x 2" high x variable length is sufficient here). Each busbar is drilled with rows of holes according to NEMA standards, for attachment of bolted compression fittings.

Telecommunications equipment, frames, cabinets and voltage protectors are typically grounded to these busbars. Busbars are connected by a backbone of insulated, solid copper cable between all closets and rooms (minimum 6 AWG, 3/0 AWG recommended). This backbone is connected to a main grounding busbar in the telecommunications entrance facility, to an earth ground in the electrical entrance facility and to structural steel on each floor. Bonding conductor cabling must be colored green or labeled appropriately.

Terms

- Telecommunications Main Grounding Busbar (TMGB)
- Telecommunications Bonding Backbone (TBB)
- Telecommunications Grounding Busbar (TGB)
- Telecommunications Bonding Backbone Interconnecting Bonding Conductor (TBBIBC)

(See schematic of grounding/bonding network on page 63.)



Technology. Services. Delivered Globally

Schematic of Grounding/Bonding Network

The Purpose of ANSI/TIA/EIA-942

Telecommunications Infrastructure Standard for Data Centers

- The purpose of this standard is to provide requirements and guideline for the design and installation of a data center or computer room.
- It is intended for designers who need a comprehensive understanding
 of the data center design including the facility planning, the cabling
 system, and the network design.
- It facilitates the planning for data centers to occur earlier in the building development process (architectural, facilities, and IT).

Data centers support a wide range of transmission protocols. Some of these protocols impose distance restrictions that are shorter than those imposed by this standard. When applying specific transmission protocols, consult standards, regulations, equipment vendors, and system service suppliers for applicability, limitations, and ancillary requirements. Consider consolidating standardized and proprietary cabling into a single structured cabling system.

The Standard Specifies:

- Cabling design
- Network design
- Facilities design
- Informative annexes containing "best practices" and availability requirements
- Spaces
- Pathways
- Racks/cahinets

Section Contents

ANSI/TIA/FIA-942

Telecommunications Infrastructure Standard for Data Centers


Data Center Cabling Infrastructure6	6
Hot and Cold Aisles	7
Horizontal Cabling6	8
Backbone Cabling6	9
Recognized Cabling Media for Horizontal	
and Backbone Applications	0
Redundancy	1

Standards Reference Guide 65

Data Center Cabling Infrastructure

The basic elements of the data center cabling system structure are the following:

- · Horizontal cabling
- · Backbone cabling
- Cross-connect in the entrance room or main distribution area
- Main Cross-Connect (MC) in the main distribution area
- Horizontal Cross-Connect (HC) in the telecommunications room, horizontal distribution area or main distribution area.
- Zone outlet or consolidation point in the zone distribution area
- Outlet in the equipment distribution area



Hot and Cold Aisles


Cabinets and racks shall be arranged in an alternating pattern, with fronts of cabinets/racks facing each other in a row to create "hot" and "cold" aisles. Cold aisles are in front of racks and cabinets. If there is an access floor, power distribution cables should be installed here under the access floor on the slab. Hot aisles are behind racks and cabinets. If there is an access floor, cable trays for telecommunications cabling should be located under the access floor in the hot aisles.

Technol ogy.

Servi ces.

Delivered Globally

A minimum of 1 m (3 ft) of front clearance shall be provided for installation of equipment. A front clearance of 1.2 m (4 ft) is preferable to accommodate deeper equipment. A minimum of 0.6 m (2 ft) of rear clearance shall be provided for service access at the rear of racks and cabinets. A rear clearance of 1 m (3 ft) is preferable. Some equipment may require service clearances of greater than 1 m (3 ft).




Hot and Cold Aisles

Horizontal Cabling

The horizontal cabling is the portion of the telecommunications cabling system that extends from the mechanical termination in the equipment distribution area to either the horizontal cross-connect in the horizontal distribution area or the main cross-connect in the main distribution area. The horizontal cabling includes horizontal cables, mechanical terminations, and patch cords or jumpers, and may include a zone outlet or a consolidation point in the zone distribution area.

The following partial listing of common services and systems should be considered when the horizontal cabling is designed:

- Voice, modem and facsimile telecommunications service
- Premises switching equipment
- Computer and telecommunications management connections
- Keyboard/Video/Mouse (KVM) connections
- Data communications
- Wide Area Networks (WAN)
- · Local Area Networks (LAN)
- Storage Area Networks (SAN)
- Other building signaling systems (building automation systems such as fire, security, power, HVAC, etc.).



Horizontal Cabling Using Star Topology


	24 AWG UTP/24	ScTP Patch Cords	26 AWG ScTI	P Patch Cords
Length of Horizontal Cable (H)	Maximum Length of Zone Area Cable (Z)	Maximum Combined Length of Zone Area Cables, Patch Cords and Equipment (C)	of Zone Area Cable (Z)	Maximum Combined Length of Zone Area Cables, Patch Cords and Equipment Cable (C)
m (ft)	m (ft)	m (ft)	m (ft)	m (ft)
90 (295)	5 (16)	10 (33)	4 (13)	8 (26)
85 (279)	9 (30)	14 (46)	7 (23)	11 (35)
80 (262)	13 (44)	18 (59)	11 (35)	15 (49)
75 (246)	17 (57)	22 (72)	14 (46)	18 (59)
70 (230)	22 (72)	27 (89)	17 (56)	21 (70)

Technol ogy.

Services. Delivered Globally

Backbone Cabling

The function of the backbone cabling is to provide connections between the main distribution area, the horizontal distribution area and entrance facilities in the data center cabling system. Backbone cabling consists of the backbone cables, main cross-connects, horizontal cross-connects, mechanical terminations and patch cord or jumpers used for backbone-to-backbone cross-connection.



Backbone Cabling Using Star Topology

Recognized Cabling Media for Horizontal and Backbone Applications Recognized cables, associated connecting hardware, jumpers, patch cords, equipment cords and zone area cords shall meet all applicable requirements specified in ANSI/TIA/EIA-568-B.2 and ANSI/TIA/EIA-568-B.3.

- 100 ohm twisted-pair cable (ANSI/TIA/EIA-568-B.2), Category 6 recommended (ANSI/TIA/EIA-568-B.2-1)
- Multimode optical fiber cable, either 62.5/125 μ or 50/125 μ (ANSI/TIA/EIA-568-B.3), 50/125 μ 850 nm laser optimized multimode fiber is recommended (ANSI/TIA-568-B.3-1)
- Single-mode optical fiber cable (ANSI/TIA/EIA-568-B.3).
- The recognized coaxial media are 75 ohm (734 and 735 type) coaxial cable (Telcordia Technologies GR-139-CORE) and coaxial connector (ANSI T1.404).

Redundancy


Data centers that are equipped with diverse telecommunications facilities may be able to continue their function under catastrophic conditions that would otherwise interrupt the data center's telecommunications service. This standard includes four tiers relating to various levels of availability of the data center facility infrastructure. The tiers are related to research conducted by the Uptime Institute, which define four tiers of performance as defined in the following table.

Technol ogy.

Delivered Globally

	Tier I: Basic	Tier II: Redundant Components	Tier III: Concurrently Maintainable	Tier IV: Fault Tolerant
Number of Delivery paths	Only 1	Only 1	1 Active, 1 Passive	2 Active
Redundant Components	N	N+1	N+1	2 (N + 1) S + S
Support Space to Raised Floor Ratio	20%	30%	80-90%	100%
Initial Watts/ft	20-30	40-50	40-60	50-80
Ultimate Watts/ft	20-30	40-50	100-150	150+
Raised Floor Height	12"	18"	30-36"	30-36"
Floor Loading Pounds/ft	85	100	150	150+
Utility Voltage	208, 480	208, 480	12-15kV	12-15kV
Months to Implement	3	3 to 6	15 to 20	15 to 20
Year First Deployed	1965	1970	1985	1995
Construction \$/ft Raised Floor	\$450	\$600	\$900	\$1,100 +
Annual IT Downtime Due to Site	28.8 hrs	22.0 hrs	1.6 hrs	0.4 hrs
Site Availability	99.671%	99.749%	99.982%	99.995%

Providing redundant cross-connect areas and pathways that are physically separated can increase the reliability of the communications infrastructure. It is common for data centers to have multiple access providers providing services, redundant routers, redundant core distribution and edge switches. Although this network topology provides a certain level of redundancy, the duplication in services and hardware alone does not ensure that single points of failure have been eliminated.



Purpose of the ISO 11801:2002 Standard

The International Standard provides:

- Users with an application independent generic cabling system capable of supporting a wide range of applications
- Users with a flexible cabling scheme so that modifications are both easy and economical
- Building professionals (for example architects) guidance on the accommodation of cabling at the initial stages of development

The International Standard specifies a multivendor cabling system which may be implemented with material from single and multiple sources, and is related to:

- International standards for cabling components developed by committees in the IEC.
- Standards for the installation and operation of information technology cabling as well as for testing of installed cabling
- Applications developed by technical committees of the IEC
- Planning and installation guides which take into account the needs of specific applications

Generic cabling defined within this International Standard:

- Specifies a cabling structure supporting a wide variety of applications
- Specifies channel and link classes A,B,C,D and E meeting the requirements of standardized applications
- Specifies channel and link classes E and F based on higher performance components to support future applications
- Specifies optical channel and link classes OF-300, OF-500 and OF-2000
- Involves component requirements and specifies cabling implementations that ensure performance of permanent links and channels that meet or exceed the requirements for cabling classes

The International Standard specifies a generic cabling system that is anticipated to have a usable life in excess of 10 years.

ISO 11801 Class EA Standard

The draft requirements for ISO (The International Organization for Standardization) Class E_A are more demanding compared to TIA/EIA Augmented Cat 6 draft requirements. Anixter's lab tests to the more stringent ISO draft standards.

ISO Compared to TIA		
Characteristics 500MHz (dB) PSNEXT LOSS	ISO Class E _A 24.8dB	TIA Augmented Cat 6 Draft 23.2dB
NEXT Loss	27.9dB	26.1dB
PSANEXT Loss	49.5dB	49.5dB
Return Loss	8.0dB	6.0dB
Insertion Loss	49.3dB	49.3dB
Referred to by IEEE	Yes	No

TIA Category 6 versus Augmented Category 6 versus ISO Class E _A				
	TIA Category 5e UTP	TIA Category 6 UTP	TIA Augmented Category 6 UTP	ISO Class E _A
Recognized	M	W	V	V.
by IEEE 802.3an	No	Yes	Yes	Yes
55 Meter				
Distance Support	No	Yes	Yes	Yes
100 Meter Distance Support	No	No	Yes	Yes
	140	110	163	163
Extrapolated Test Limits for NEXT and PSNEXT				
to 500MHz	No	No	No	Yes

This table summarizes the various UTP cabling options and their respective 10 Gigabit performance attributes as defined by the latest draft standards. Category 5e is not recognized as a viable cabling media to support 10 Gigabit transmission regardless of its installed cabling distance. Category 6 cabling will only support 10 Gigabit at a maximum installed distance of 55 meters. Today, the only options for operating 10 Gigabit at 100 meters are the TIA Augmented Category 6 and ISO Class EA standards. ISO's Class EA system has superior return loss, NEXT and PSNEXT performance values when compared with the current TIA Augmented Category 6 draft proposals.

The Anixter European Standards Reference Guide

The Anixter European Standards Reference Guide is an invaluable industry tool to help you stay informed of recent developments in standards for structured cabling systems. The guide includes an up-to-date summary of the ANSI/TIA/EIA, ISO, CENELEC and IEEE standards featuring European standards ISO 11801, ISO 18010, EN50173, EN50174, EN50310.

To order a copy, go to www.anixter.com/literature.

IEEE's 802.3af Power over Ethernet (PoE) Standard

The IEEE's 802.3af specification calls for power source equipment (PSE), which operates at 48 volts of direct current. This guarantees 12.95 watts of power over unshielded twisted-pair cable to data terminal equipment (DTE) 100 meters away (the maximum distance supported by Ethernet). That's enough power to support IP phones, WLAN access points and many other DTE devices. Two PSE types are supported including Ethernet switches equipped with a power supply module called end-span devices and a special patch panel called a midspan device, that sits between a legacy switch and powered equipment, injecting power to each connection.

IEEE's 802.11 Wireless Standard

IEEE 802.11, the Wi-Fi standard, denotes a set of wireless LAN/WLAN standards developed by working group 11 of the IEEE LAN/MAN standards committee (IEEE 802). The term 802.11x is also used to denote this set of standards, and is not to be mistaken for any one of its elements. There is no single 802.11x standard.

802.11 details a wireless interface between devices to manage packet traffic (to avoid collisions, etc.). Some common specifications and their distinctive attributes include the following:

802.11a — Operates in the 5 GHz frequency range (5.125 to 5.85 GHz) with a maximum 54 Mbps signaling rate. The 5 GHz frequency band isn't as crowded as the 2.4 GHz frequency because it offers significantly more radio channels than the 802.11b and is used by fewer applications. It has a shorter range than 802.11g, is actually newer than 802.11b and is not compatible with 802.11b.

802.11b – Operates in the 2.4 GHz industrial, scientific and medical (ISM) band (2.4 to 2.4835 GHz) and provides signaling rates of up to 11 Mbps. This is a very commonly used frequency. Microwave ovens, cordless phones, medical and scientific equipment, as well as Bluetooth® devices, all work within the 2.4 GHz ISM band.

802.11e — Ratified by the IEEE in late September of 2005, the 802.11e quality-of-service specification is designed to guarantee the quality of voice and video traffic. It will be particularly important for companies interested in using Wi-Fi phones.

802.11g — Similar to 802.11b, but this standard supports signaling rates of up to 54 Mbps It also operates in the heavily used 2.4 GHz ISM band but uses a different radio technology to boost overall throughput. Compatible with older 802.11b.

802.11i — Also sometimes called Wi-Fi Protected Access 2 (WPA 2), 802.11i was ratified in June 2004. WPA 2 supports the 128-bit -and-above Advanced Encryption Standard, along with 802.1x authentication and key management features.

Products. Technology.

Services. Delivered Globally

802.11k — Predicted for ratification in mid-2007, the 802.11k Radio Resource Management Standard will provide measurement information for access points and switches to make wireless LANs run more efficiently. It may, for example, better distribute traffic loads across access points or allow dynamic adjustments of transmission power to minimize interference.

802.11n – The Standard for Enhancements for Higher Throughput is designed to raise effective WLAN throughput to more than 100 Mbps Final ratification is expected in late 2007.

IEEE 802.3an Standard

IEEE 802.3an Standard				
IEEE Model 1	Standard ISO Class F (individual shields)	Media S/FTP	Distance 100m	
	ISO Class E _A	UTP	100m	
	TIA Augmented Cat 6	UTP	100m	
2,3,4	Shielded Cat 6 (overall shield)	F/UTP, ScTP, STP	100m	
	TIA Standard Cat 6/ ISO Class E	UTP	< 55m	

ANSI/EIA/TIA-568-B.2-ad10 (Augmented Category 6) and ISO 11801 (Class EA) cable specifications are based on IEEE models.

The IEEE created four models, which specify distance limitations based on media types.

100 meters over UTP is only guaranteed when using Augmented Category 6 or ISO Class EA compliant cabling systems.

TIA-568-B.2-ad10 Augmented Cat 6 or ISO 11801 Class EA cables.

10 Gigabit Ethernet Channel Applications				
Application Data Center (Server Clustering)	10GBase Fiber (802.3ae) YeS	10GBase-T Yes	10GBase-CX4 (802.3ak) Yes (< 15m)	
Horizontal (In Building)	No	Yes	No	
Vertical (Risers)	Yes	No	No	
Campus/Metro	Yes	No	No	

In the chart above, the recommended application roadmaps for 10 Gigabit Ethernet cabling and protocol types have been provided. The choice of which media to use will revolve around three variables:

- Circuit distances
- Cost
- Active equipment interfaces (connectors).

10GBASE Fiber will maintain traditional application in backbones and risers and also in the data center for server clustering.

10GBASE-T copper will remain in the traditional areas of application (in horizontal building cabling but also in the data center between servers and clusters).

10GBASE-CX4 defines a multi-conductor copper solution primarily designed to connect servers and switches over short distances.

Products. Technology.

Servi ces.

Delivered Globally

1. 800. Ani xter.

Anixter's Enterprise Cabling and Security Labs

At Anixter, making sure our customers have the most current and accurate information to select the right products for their specific applications is paramount to us. We own and operate two labs, the UL®— certified Enterprise Cabling Lab and the Security Lab, specifically to evaluate and test a wide range of emerging new products and technologies being developed and marketed. Our labs give our customers the ability to preview how their new products will actually perform before purchasing them.

Enterprise Cabling Lab Testing:

- Random performance testing of Anixter inventory to ensure quality of standards compliance
- Network throughput and interoperability testing
- Copper and fiber cabling compliance verification (TIA/EIA, ISO/IEC, IEEE)
- Customer proof of concept
- Power over Ethernet (PoE)
- Application testing

Security Lab Testing:

- Video over IP, video quality and bandwidth utilization
- Power over Ethernet (PoE) capability verification
- Digital compression image quality vs. analog technology testing
- Evaluation of analog and IP cameras, video management software evaluation, DVR, NDVR and NVR products

Business Drivers Affecting the Purchase of Enterprise Cabling Products:

- New applications
- Higher bandwidth requirements
- Convergence
- Maintain competitive edge
- Cost of moves, adds, and changes (MACs)
- Business process efficiencies

Business Drivers Affecting the Purchase Security Products:

- Convergence of IT and security
- Analog to digital technology shift
- Loss prevention
- Systems integration
- Preventative security precautions
- Asset protection

Anixter's Enterprise Cabling and Security Labs In Action

Products. Technology.

Servi ces.

Delivered Globally

Problem: Leading Pennsylvania University Explores Campus-wide Rewiring Project

Anixter Enterprise Cabling Lab Solution: The Anixter Enterprise Cabling Lab was called upon to help this university determine which copper cabling system would best meet their current and future information technology needs. The university had a variety of different copper cabling products installed in their network infrastructure — Category 3, Category 5 and some Category 5e. The Anixter Enterprise Cabling Lab deployed computer applications that the university typically carried over their cabling infrastructure including Lotus Notes, SAP and streaming video. Testing found that their current infrastructure was consistently dropping information causing the network to operate slowly and inefficiently. This same traffic was sent over a Category 6 infrastructure with no degradation to the data. Armed with testing from the Anixter Enterprise Cabling Lab, university IT professionals wrote cabling infrastructure specifications around a higher performing Category 6 system that better met the university's network performance needs.

Problem: Major Railway Company Needs Video Surveillance To Monitor Switchyard

Anixter Security Lab Solution: This railroad wanted to use video surveillance to monitor yards as they assembled unit trains, but had a big cabling challenge in front of them. Installing traditional cabling in the switchyard would have entailed major disruptions and expense for the customer. The Anixter Security Lab recommended a sophisticated wireless internet video surveillance system that did not require cabling. Anixter was able to simulate the wireless internet video surveillance solution in the Security Lab for the customer. The Security Lab also provided this customer with test results illustrating how much bandwidth the video solution would absorb on the customer's network as well as the video quality the customer could expect from the recommended system.

Problem: National Insurance Company with Data Center Cabling Choice

Anixter Enterprise Cabling Lab Solution: The Anixter Enterprise Cabling Lab assessed backbone cabling requirements based on the current and future bandwidth needs for this insurance provider. The Anixter Enterprise Cabling Lab ran representative network traffic over 62.5, 50-micron and laser-optimized 50-micron fiber (LOMF) to ascertain which would best meet their needs. These tests were key in determining that the LOMF was the customer's best choice.

Anixter's 10 Gig Ethernet Cabling Testing

Anixter Enterprise Cabling Lab is the only UL-certified lab to conduct rigorous, independent third party testing of the emerging 10 Gig cabling solutions. Anixter's 10 Gig cabling testing examines electrical characteristics such as insertion loss, return loss, and crosstalk, but also looks at alien crosstalk (which is part of the Augmented Cat 6 draft spec.) To ensure that the 10 Gig cabling solutions we sell meet the highest levels of performance and reliability for our customers, the Anixter Enterprise Cabling Lab tests the toughest performance parameter, alien crosstalk, in the "worst case" scenario. You can rest assured that the cabling solutions Anixter sells will provide the network performance you require.

Technol ogy.

Servi ces.

Delivered Globally



Reference Documents for Further Information on Cabling Standards

TIA/EIA-568-B.1 (2001)

Commercial Building Telecommunications Cabling

Standard Part 1: General Requirements

TIA/EIA-568-B.2 (2001)

Commercial Building Telecommunications Cabling

Standard Part 2: Balanced Twisted Pair Cabling Components

TIA/EIA-568-B.2-1 (2002)

Transmission Performance Specifications for 4-pair 100_Ω

Augmented Category 6 Cabling

TIA/EIA-568-B.2-ad10 (Draft)

Transmission Performance Specifications for 4-pair 100Ω Augmented Category 6 Cabling

TIA/EIA-568-B.3 (2000)

Optical Fiber Cabling Components Standard

TIA/EIA-569-B (2004) (CSA T530)*

Commercial Building Standard for Telecommunications Pathways and Spaces

TIA/EIA-570-A (1999) (CSA T525)*

Residential and Light Commercial Telecommunication Wiring Standard

TIA/EIA-606-A (2002) (CSA T528)*

Administration Standard for the Telecommunications Infrastructure of Commercial Buildings

J-STD-607-A (2002) (CSA T527)*

Commercial Building Grounding/Bonding Requirements for Telecommunications

*Canadian Standards Association equivalent document

TIA/EIA-758 (1999)

Customer-owned Outside Plant Telecommunications Cabling Standard

Technol ogy.

Servi ces.

Delivered Globally

TIA/EIA-942 (2005)

Telecommunications Infrastructure Standard for Data Centers

ISO/IEC 11801 (2002)

Generic Cabling for Customer Premises

IEEE 802.3-1998 (1998)

Carrier Sense Multiple Access with Collision Detection (CSMA/CD)

Access Method and Physical Layer Specification (also known as ANSI/IEEE Std 802.3-1998 or ISO 8802-3: 1990 (E))

IEEE 802.3an (2006)

Physical Layer and Management Parameters for 10 Gb/s Operation, Type 10GBase-T

IEEE 802.5-1998 (1998)

Token Ring Access Method and Physical Layer Specifications (also known as ANSI/IEEE Std 802.5-1998)

Obtaining Standards Documents

TIA/EIA documents may be purchased through Global Engineering
Documents at 1-800-854-7179 or www.global.ihs.com. IEEE documents
may be purchased through IEEE, P.O. Box 1331, Piscataway, NJ 08855
or www.ieee.org. CSA documents may be purchased through the Canadian
Standards Association at www.csa.ca or by calling (416) 747-4000.

For further assistance or more information, contact your local Anixter sales office or 1-800-ANIXTER. Some material in this publication is reproduced from standards publications which are copyrighted by the Telecommunications Industry Association.

This handbook was prepared by Anixter Inc., which is not affiliated with the Telecommunications Industry Association or the Electronic Industries Alliance. Neither EIA nor TIA are responsible for the content of this publication.

For direct assistance in interpreting telecommunications standards, consider Registered Communications Distribution Designers (RCDD) certified by the Building Industry Consulting Service International (BICSI) at (800) 242-7405 or www.bicsi.org. Hundreds of Anixter technical professionals are registered with BICSI.

The Anixter European Standards Reference Guide

The Anixter European Standards Reference Guide is an invaluable industry tool to help you stay informed of recent developments in standards for structured cabling systems. The guide includes an up-to-date summary of the ANSI/TIA/EIA, ISO, CENELEC and IEEE standards featuring European standards ISO 11801, ISO 18010, EN50173, EN50174, EN50310.

To order a copy, go to www.anixter.com/literature.

Technol ogy.

Services, Delivered Globally

W0001Z1 © 2006 Anixter Inc. • 10/06 • 5K • 251937

AVIXE

Enterprise Cabling and Security Solutions • Electrical and Electronic Wire & Cable • Fasteners • Supply Chain Services Anixter Inc. • 1.800.ANIXTER • anixter.com • World Headquarters: 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 224.521.8000

Anixter Inc. is the world's leading supplier of Supply Chain Services and products used to connect voice, video, data and security systems. Anixter is also the leading provider of specialty electrical and electronic wire and cable for building construction, industrial maintenance and repair, and original equipment manufacturing, as well as the leader in providing fasteners and "C" Class components to OEMs and production lines. We bundle our products with our innovative Supply Chain Services to help control the cost of our customers' business processes, reduce their investment in inventory, and ensure they get the right product when they need it. A publicly held company, Anixter, with its subsidiaries, serves companies in more than 45 countries around the world.

Anixter's total revenue exceeds \$3.8 billion.

Anixter Inc. does not manufacture the items described in this publication. All applicable warranties are provided by the manufacturers. Purchasers are requested to determine directly from the manufacturers the applicable product warranties and limitations. Data and suggestions made in the publication are not to be construed as recommendations or authorizations to use any products in violation of any government law or regulation relating to any material or its use.